


Deep groove ball bearings, single row, seal on both sides

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
40	80	18	32,5	19	0,8	-	5600	0,37	6208-2RS1 *



Calculation factors

k_r 0,025

f_0 14