

## AD1938

КОЛ-ВО	ПОЗИЦИЯ	НАИМЕНОВАНИЕ	КОД ТОВАРА
4	U1, U2, U3, U4	ADA4841-2YRMZ	9000047305
1	U5	AD1938WBSTZ	9000556455
1	D1	ADM6316BX30ARJZ-R7	9000524433
1	U6	TJ9198GSF5-3.3D	9000543850
1	Y1	12.288 МГц имп. HC-49U	44665
8	C1, C2, C3, C4 C26, C29, C32, C35	100p 0603	305749128
18	C5, C6, C7, C8 C17, C18, C19, C20, C21 C22, C23, C24, C41, C44, C45, C46, C54, C61	10uF 0603	9000103925
5	C13, C14, C15, C16, C63	390p 0603	853846858
2	C51, C60	22p 0603	183744283
16	C25, C27, C28, C30, C31, C33, C34, C36, C50, C53, C56, C59, C62, C64, C66, C67	2n2 0603	749687185
15	C9, C10, C11, C12, C37, C38, C39, C40, C42, C43, C47, C48, C49, C55, C57	0.1 0603	226236018
2	C52, C58	47 uF тип В	366405224
1	C65	5600p 0603	526352732
1	L1	NBQ160808T-601Y-N, 0603, 600 Ом	9000523891
4	R1, R2, R3, R4	100k 0603	9000079760
12	R9, R10, R11, R12, R25, R26, R27, R28, R29, R30, R31, R32	100R 0603	9000079616
4	R33, R34, R43, R44	51R 0603	9000079609
8	R35, R 36, R37, R38, R39, R40, R41, R42	470R 0603	9000079668
16	R5, R6, R7, R8, R13, R14, R15, R16, R17, R18, R19, R20, R21, R22, R23, R24	4,7K 0603	9000079728
2	RN1, RN2	4 x 51R 0603	460341196
4		MJ-C-6.5 (DS1027-2B)	9000215966

1	Печатная плата		9000575824