

Specifications	UT658
Input voltage range (V)	3V~9V
Voltage resolution	0.01V
Voltage monitoring accuracy	±1%
Current monitoring range (A)	0A~3A
Current monitoring accuracy	±(1%±2)
Current resolution	0.01A
Capacity	0~9999mAH
Capacity data storage	10 sets
Display	LCD
Warning	√
Button	√
Cable length	
Pollution level	2
Working temperature	0°C~40°C
Storage temperature	-10°C~50°C
Relative humidity	<75%
General Characteristics	
Product color	White
Product net weight	28g
Product size	84mm x 29mm x 12mm
Standard individual packing	Blister, insert card
Standard quantity per carton	100pcs
Standard carton measurement	185mm x 180mm x 185mm
Standard carton gross weight	3.3kg