

MILAN S.r.l. a socio unico

Head Office – Export department:  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it



Even in White

## Technical Datasheet

# tasker® RG 59 Flex -Coaxial Cable 75 Ω



	A	B	C	D
--	---	---	---	---

**CATEGORY**  
**APPLICATIONS**

Coaxial cable 75 Ω (See Video Catalogue)  
 Premade video Cables and Broadcast.

- A:** PVC Sheath available in different color.  
Outer cable Diam. Ø 6,10 (±0,10) mm.
- B:** Shielding in O.F.C. red copper braid covering 90% .
- C:** Core Insulation with transparent PE. Diam. Ø 3,70 (±0,10) mm.
- D:** Stranded O.F.C. red copper formation 7x0,20 mm.  
Nom. Cross section 1x0,22 mm<sup>2</sup>.

**MARKING**  
**AVAILABLE ALSO**

**tasker®** RG59 FLEX 75Ω BROADCAST VIDEO CABLE  
 RG59 BU, RG59 Extra, RG59 LSZH, RG59 Special, RG59 PUR,  
 RG59 AR

**CUSTOM**  
**PRODUCTION**

This product may be custom produced also in **PE**, with or without  
 Metallic Armor.

**Cable Properties**

<b>Conductor Resistance</b>	75 Ω/Km
<b>Capacity Core/Shield</b>	67 pF/mt
<b>Velocity of Propagation</b>	66%
<b>Impedance</b>	75 Ω
<b>Max Rated Voltage</b>	2.000 V
<b>Operative Temperature</b>	-15/+70°C

**Attenuation dB/100 m.**

<b>50 MHz</b>	7,4
<b>100 MHz</b>	10,7
<b>200 MHz</b>	15,7
<b>400 MHz</b>	22,7
<b>800 MHz</b>	33,6
<b>1000 MHz</b>	38,0

<b>USE</b>	<b>X</b>	Indoor	Interno Edificio
<b>Impiego</b>		Outdoor Limited	Esterno Limitato
		Outdoor	Esterno
		Outdoor Direct Burial	Esterno Interrato

<b>INSTALLATION</b>	<b>X</b>	Fixed	Fissa
<b>Posa</b>	<b>X</b>	Restricted Mobile	Mobile Limitata
		Mobile	Mobile
		Mobile in Drag Chain	Mobile in Catena

<b>INFORMATION</b>	<b>X</b>	RoHS2 Compliant
<b>Informazioni</b>	<b>X</b>	Ver. A / 16.05.16