



MATERIAL & FINISHES
 INSULATOR - PBT GLASS FILLED UH94V-0
 STANDARD COLOR: Blue
 CONTACT BRASS OR PHOSPHOR BRONZE
 SHELL - STEEL
 PLATING - CONTACT

SELECTIVE 3u" GOLD OVER NICKEL PLATED (CONTACT AREA)
 TIN/LEAD OVER NICKEL PLATED (TAIL AREA)
 - SHELL
 Nickel or Tin COPPER PLATED

ELECTRICAL CHARACTERISTICS

RATING CURRENT : 3A
 CONTACT RESISTANCE : <15mΩ
 INSULATION RESISTANCE : <3000MΩ AC 500V
 DIELECTRIC VOLTAGE : 1000V AT 1 MINUTE
 OPERATING TEMPERATURE : -55° C TO+105° C

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:											
CHECKED:	DATE:											
DRAWN:	DATE:	TITLE: DBH-18P 公头 三排 单线式 接触端子 镀金3u"										
LYF	2014-11-17	<table border="1"> <tr> <td>PART. NO.</td> <td></td> </tr> <tr> <td>UNIT</td> <td>mm</td> </tr> <tr> <td>SCALE</td> <td>free</td> </tr> <tr> <td>FILE NO.</td> <td>S007200356</td> </tr> <tr> <td>REV.</td> <td>A XH00</td> </tr> </table>	PART. NO.		UNIT	mm	SCALE	free	FILE NO.	S007200356	REV.	A XH00
PART. NO.												
UNIT	mm											
SCALE	free											
FILE NO.	S007200356											
REV.	A XH00											