

FEATURES

- 75mm wheel diameter
- 90kg load capacity
- Zinc plated body
- Medium Duty Range with bright zinc finish
- Pressed steel bracket

RS PRO Swivel Swivel Castor, 90kg Load Capacity, 75mm Wheel Diameter

RS Stock No.: 687-310



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO range of castors for medium duty applications which feature a top plate fixing type which allows for easy fixing to the bottom of objects

Options include:

196-4933 - Rubber tyre fixed castor, 83x35 mm hole centres

687-310 - Rubber tyre swivel castor, 80x60 mm hole centres

687-326 - Rubber tyre swivel castor with foot brake, 80x60 mm hole centres

General Specifications

Rotation	Swivel
Load Capacity	90kg
Tyre Material	Hub black nylon, with blue rubber tyre
Hub Material	Nylon
Includes Brake	No
Features	Non-Marking
Applications	Trucks and Trolleys, Workbenches, Furniture, Racks

Mechanical Specifications

Wheel Diameter	75mm
Wheel / Tread Width	32mm
Overall Height	95mm
Number of Fixing Holes	4
Fixing Hole Size	8mm
Hub Bearing Type	Plain

Fixing Centres Specifications

Fixing Centres	80/86mm x 60mm
-----------------------	----------------

Fixing Plate Specifications

Fixing Plate Dimensions	105mm x 80mm
--------------------------------	--------------

