



Fuse-link, high speed, 6 A, AC 600 V, 200 kA, 10 x 38 mm, aR, UL

Part no. **6AMP 600V AC FERRULE 10 X 38MM**  
 Catalog No. **FWC-6A10F**

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	6
Rated voltage			AC 600 V
Size			10 x 38 mm
Utilization category			aR
Breaking Capacity		kA	200
usable for size/applications			DC common bus, DC drives, power converters/rectifiers and reduced voltage starters
Standard/Approval			UL
Shape			cylindrical
Standards/Regulations			UL 248
Optional accessories			fuse-holder CHM1DU

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss10.0.1-27-14-20-02 [AFZ797013])			
Size			10x38 mm
Rated voltage		V	600 - 600
Rated voltage			Other
Voltage type			AC/DC
Utilization category			aR (accompanied semiconductor protection)
Rated operating frequency		Hz	45 - 62
Nominal current		A	6
With striker			No
Release characteristic			Other
Breaking capacity		kA	200