



H3DK-S2 24-240VAC/DC

Timer, DIN-rail mounting, multi range, multi mode timer, 4 modes, 2 output relays, 24 to 240 VAC/DC

Specifications

| | |
|---------------------|---|
| Type | Analog |
| Installation type | DIN Rail |
| Functions | Multi-functional |
| Size | 22.5 mm |
| Terminal | Screw |
| Operating mode | Flicker ON Start (Power ON Start), Interval (Power ON Start), ON Delay (Power ON Start), One-shot Output (Power ON Start) |
| Output type | Relay |
| Contact description | DPDT |
| Time range | 0.1 s - 1200 h |
| Supply voltage AC | 24-240 V |
| Supply voltage DC | 24-240 V |

Downloads

CAD Library



H3DK Solid-state Timers Datasheet

EN PDF 5.93 MB



Timers Brochure

EN PDF 9.85 MB

