



H3DS-ML AC/DC

Timer, DIN rail mounting, 17.5 mm, 24-230 VAC/24-48 VDC, multifunction, 0.1 s-120 h, SPDT, 5 A, 'Smart Dial' lockable settings

Specifications

Type	Analog
Installation type	DIN Rail
Functions	Multi-functional
Size	17.5 mm
Terminal	Screw
Operating mode	Flicker OFF Start (Power ON Start), Flicker OFF Start (Signal Start), Flicker ON Start (Power ON Start), Flicker ON Start (Signal Start), Interval (Power ON Start), Interval (Signal Start), ON Delay (Power ON Start), ON Delay (Signal Start), One-shot Output (Power ON Start), One-shot Output (Signal Start), Signal ON/OFF Delay
Output type	Relay
Contact description	SPDT
Time range	0.1 s - 120 h
Supply voltage AC	24-230 V
Supply voltage DC	24-48 V

Accessories



Y92S-38

Adjustment and locking tool for H3DS

CAD Library



H3DS Solid-state Timer Datasheet

EN PDF 2.66 MB



Screwless Clamp Brochure

EN PDF 418 KB



Timers Brochure

EN PDF 9.85 MB