



SECTION A-A
CUSTOMER DRAWING

NOTES:

1. RECOMMENDED MOUNTING HOLE: Ø1.000 [25.40].
2. IP68 RATED WHEN PROPERLY ASSEMBLED. IMMERSED IN 1.8M WATER FOR 24 HOURS.
3. PARTS ARE SHIPPED ASSEMBLED.
4. CABLE RANGE: Ø0.118– 0.236 [3.0-6.0] - TYP 3 PLACES.
5. MATERIALS:
 SEAL NUT, CLAMP NUT, HEX NUT - BLACK, THERMOPLASTIC UL746C (F1) UV RATED
 GASKET, SEAL RING AND SEAL PLUGS - BLACK, SILICONE.
6. THIS PRODUCT IS RoHS COMPLIANT.

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
					UNLESS OTHERWISE SPECIFIED	SIZE	WIDTH	MULT	LBS/M	TEMPER
					1. ALL DIMENSIONS IN INCHES [mm]	FINISH			MATERIAL	
					- TWO PLACE DECIMALS ±0.02 [0.5]	SPEC No.			SPEC No.	
					- THREE PLACE DECIMALS ±0.005 [0.13]	FIRST USED ON			SCALE 1:1	
C	28375	03/30/21	PC	TJK	DO NOT SCALE DRAWING	DATE DRAWN	BY	CHKD	APVD	
B	28315	09/09/20	PC	TJK		5/6/20	FM	FM	TJK	
A	28308	07/31/20	PC	TJK		5/6/20	FM	5/6/20	7/16/20	
REV	ECO NUMBER	DATE	BY	APVD		NAME M25 x 1.5 CABLE GLAND, 3 HOLE, CABLE RANGE Ø3.0 - 6.0mm			PART No.	REV
REVISIONS									CGM25N24X3	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[CGM25N24X3](#)