

LOUDITY

SPECIFICATION SHEET

MODEL	LD-SP-5032
Power (Nominal)	0.25 Watts
Power (Maximum)	0.5 Watts
Impedance	$32 \pm 15\%$ ohms
Resonant Frequency	$600 \pm 20\%$ Hz
Sound Pressure Level 1W, 0.5m Average at 0.8, 1.0, 1.2, 1.5KHz	88 ± 3 dB
Frequency Range	fo-4500 Hz
Cone Materials	Black Paper
Magnet Materials: NdFeB	$\varnothing 12.5 \times 2.5$ mm
Housing materials:	Metal
Operating Temperature Range	-20° to $+60^{\circ}$ C
Storage Temperature	-30° to $+70^{\circ}$ C
Weight	$18g \pm 5\%$

DIMENSIONS unit: mm

