


## Polyurethane recoils with rigid and swiveling male fittings



### Technical characteristics

**Max operating pressure:** 8 bar

**Temperature:** -15°C to +70°C

**Construction:** Polyurethane

**Highlight:** Non scratch

**Equipped with:** Teflon-coated coupler

Black

BSPT male thread	ID/OD (mm)	Coil Ø (mm)	Max length (m)	Min. length (m)	Parts Numbers
R 1/4	6.5 x 10	42	4	0.4	<b>PUS 64NR</b>
R 1/4	6.5 x 10	52	6	0.63	<b>PUS 66NR</b>