


WRAPOST RECEPTACLES

FOR .015" - .025" DIAMETER PINS

1702/1703

170X-X-15-XX-30-XX-02-0

Press-fit in .057 mounting hole




Basic Part Number	# of Wraps	Length A
1702-2	2	.370
1703-3	3	.510

0038 ⇔ 0040/0066 ⇔ 0068

00XX-X-17-XX-30-XX-02-0

Press-fit in .057 mounting hole




Basic Part #	# of Wraps	Length A	Dia. C
0040-1	1	.260	.072
0039-2	2	.360	
0038-3	3	.500	
0068-1	1	.260	.062
0067-2	2	.360	
0066-3	3	.500	

0086/0088/0089

008X-X-17-XX-3X-XX-02-0

Press-fit in .057 mounting hole




Basic Part Number	# of Wraps	Length A
0089-2	2	.370
0088-3	3	.510
0086-4	4	.630

1030 ⇔ 1036

103X-X-17-XX-3X-XX-02-0

Press-fit in .057 mounting hole




Basic Part #	# of Wraps	Length A	Dia. C
1032-1	1	.260	.072
1031-2	2	.360	
1030-3	3	.510	
1036-1	1	.260	.062
1035-2	2	.360	
1034-3	3	.510	

1045

1045-3-17-XX-30-XX-02-0


Press-fit in .043 mounting hole



1040

1040-3-17-XX-30-XX-02-0

Press-fit in .056 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: ±.005

Diameters: ±.002

Angles: ±2°



ORDER CODE: XXXX - X - 17 - XX - XX - XX - 02 - 0

BASIC PART # →

SPECIFY SHELL FINISH: →

- 01 200 μ" TIN/LEAD OVER NICKEL
- ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ" GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH: →

- 02 100 μ" TIN/LEAD OVER NICKEL
- ◆ 84 100 μ" TIN OVER NICKEL (RoHS)
- ◆ 27 30 μ" GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#30 or #32 CONTACT (DATA ON PAGE 253)

(For alternate contact choices, see groups B and C on page 248)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0089-2-17-15-30-27-02-0](#) [1703-3-17-01-30-02-02-0](#) [1703-3-17-01-30-27-02-0](#) [1702-2-17-01-30-02-02-0](#) [1702-2-17-01-30-27-02-0](#) [1045-3-17-80-30-84-02-0](#) [1045-3-17-80-30-27-02-0](#) [1040-3-17-80-30-84-02-0](#) [1040-3-17-80-30-27-02-0](#) [1036-1-17-80-30-84-02-0](#) [1036-1-17-80-30-27-02-0](#) [1035-2-17-80-30-84-02-0](#) [1035-2-17-80-30-27-02-0](#) [1034-3-17-80-30-84-02-0](#) [1034-3-17-80-30-27-02-0](#) [0089-2-17-80-32-84-02-0](#) [0089-2-17-80-32-27-02-0](#) [0089-2-17-80-30-84-02-0](#) [0089-2-17-80-30-27-02-0](#) [0088-3-17-80-32-84-02-0](#) [0088-3-17-80-32-27-02-0](#) [0088-3-17-80-30-84-02-0](#) [0088-3-17-80-30-27-02-0](#) [0086-4-17-80-30-84-02-0](#) [0086-4-17-80-30-27-02-0](#) [0068-1-17-80-30-84-02-0](#) [0068-1-17-80-30-27-02-0](#) [0067-2-17-80-30-84-02-0](#) [0067-2-17-80-30-27-02-0](#) [0066-3-17-80-30-84-02-0](#) [0066-3-17-80-30-27-02-0](#) [0040-1-17-80-30-84-02-0](#) [0040-1-17-80-30-27-02-0](#) [0039-2-17-80-30-84-02-0](#) [0039-2-17-80-30-27-02-0](#) [0038-3-17-80-30-84-02-0](#) [0038-3-17-80-30-27-02-0](#) [0038-3-17-15-30-27-02-0](#) [0040-1-17-15-30-27-02-0](#) [0039-2-17-15-30-27-02-0](#) [0038-3-17-01-30-27-02-0](#) [0039-2-17-01-30-27-02-0](#) [0040-1-17-01-30-27-02-0](#) [1045-3-17-01-30-02-02-0](#) [1045-3-17-01-30-27-02-0](#) [1040-3-17-01-30-02-02-0](#) [1040-3-17-01-30-27-02-0](#) [1036-1-17-01-30-02-02-0](#) [1036-1-17-01-30-27-02-0](#) [1035-2-17-01-30-02-02-0](#) [1035-2-17-01-30-27-02-0](#) [1034-3-17-01-30-02-02-0](#) [1034-3-17-01-30-27-02-0](#) [0089-2-17-01-32-02-02-0](#) [0089-2-17-01-32-27-02-0](#) [0089-2-17-01-30-02-02-0](#) [0089-2-17-01-30-27-02-0](#) [0088-3-17-01-32-02-02-0](#) [0088-3-17-01-32-27-02-0](#) [0088-3-17-01-30-02-02-0](#) [0088-3-17-01-30-27-02-0](#) [0086-4-17-01-30-02-02-0](#) [0086-4-17-01-30-27-02-0](#) [0068-1-17-01-30-02-02-0](#) [0068-1-17-01-30-27-02-0](#) [0067-2-17-01-30-02-02-0](#) [0067-2-17-01-30-27-02-0](#) [0066-3-17-01-30-02-02-0](#) [0066-3-17-01-30-27-02-0](#) [0040-1-17-01-30-02-02-0](#) [0039-2-17-01-30-02-02-0](#) [0038-3-17-01-30-02-02-0](#) [0066-3-17-15-30-27-02-0](#) [0067-2-17-15-30-27-02-0](#) [0086-4-17-15-30-27-02-0](#) [0088-3-17-15-30-27-02-0](#) [0088-3-17-15-32-27-02-0](#) [0089-2-17-15-32-27-02-0](#) [1034-3-17-15-30-27-02-0](#) [1035-2-17-15-30-27-02-0](#) [1036-1-17-15-30-27-02-0](#) [1040-3-17-15-30-27-02-0](#) [1045-3-17-15-30-27-02-0](#) [1702-2-17-15-30-27-02-0](#) [1703-3-17-15-30-27-02-0](#) [1702-2-17-00-00-00-02-0](#) [1703-3-17-00-00-00-02-0](#) [1702-2-17-01-30-14-02-0](#) [1034-3-17-01-30-14-02-0](#) [1040-3-17-01-30-14-02-0](#) [1036-1-17-01-30-14-02-0](#) [1703-3-17-01-30-14-02-0](#) [1034-3-17-80-30-14-02-0](#) [0088-3-17-80-32-14-02-0](#) [0086-4-17-01-30-14-02-0](#) [0040-1-17-80-30-14-02-0](#) [0039-2-17-01-30-14-02-0](#) [0038-3-17-80-30-14-02-0](#) [0038-3-17-01-30-14-02-0](#) [0067-2-17-01-30-14-02-0](#)