

**SAK Series  
Q 10 SAK2.5****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

This type of cross-connection has a pre-assembled captive cross-connection lug, cross-connection sleeve and fixing screw.

All the individual parts are available separately on request.

During installation, the pre-assembled cross-connectors are simply placed in the cross-connection slot in the middle of the terminal and screwed tight.

**General ordering data**

Type	Q 10 SAK2.5
Order No.	<a href="#">0368700000</a>
Version	SAK Series, Cross-connector, for cross-connection link, No. of poles: 10
GTIN (EAN)	4008190107796
Qty.	20 pc(s).

**Data sheet**

**SAK Series  
Q 10 SAK2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	60.6 mm	Height	6 mm
Depth	20.5 mm	Net weight	17.5 g

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Version	for cross-connection link		

**Rated data**

Rated current	24 A
---------------	------

**Material data**

Colour	Grey
--------	------

**System specifications**

Product family	SAK Series	Mounting rail	none
----------------	------------	---------------	------

**Classifications**

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

**Product information**

Descriptive text technical data	Current-carrying capacity up to 41 A via the cross-connection, max. 6 mm <sup>2</sup>
---------------------------------	---

**Approvals**

Approvals



ROHS	Conform
------	---------