

Empty enclosure

# TG ABS 1608-6-o



## TG ABS 1608-6-o

Empty enclosure

CUSTOMIZABLE

Productnumber: 10040601

Dimensions: 162 x 82 x 55 mm

Empty enclosure IP66 / IP67 ABSAccessories supplied: Cover retainer, 4 fastening screws for accessories

**Box and cover ABS grey similar to RAL 7035, with quick closing, with cover retainer**



To industrial product:

<https://www.spelsberg.com/p/20040601>

## Technical Data

### electrical characteristics

Protection type UL:	not specified
Rated insulation voltage AC:	690 V
Rated insulation voltage DC:	1000 V
Type of protection:	IP66/IP67
Protection class:	II

### Colours

Base unit colour:	grey
Cover colour:	grey

### Dimensions

Width:	162 mm
Length:	82 mm

## Dimensions

Height:	55 mm
---------	-------

## Material characteristics

suitable for exterior use:	no
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Halogen free:	yes
Industry quality:	no

## mechanical properties

Type of fastening:	Wall/ceiling mounting
Stackable:	yes
Impact strength:	IK07

## Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

## Material

Base unit material:	ABS
Cover material:	ABS
Sealing material:	Polyurethane
Cover screw material:	Stainless steel V2A

## Accessories

[18200201 - TG ABL - External fixing lugs kit](#)

[18200401 - TG PST1 - Sealing kit](#)

[18200601 - TG DVS-42 - Cover retainer](#)

[18600601 - TG MPI-1608 - Mounting plate](#)

[18700601 - TG MPS-1608 - Mounting plate](#)

[19599501 - LFR - Stepped drill](#)

[19714601 - TS 15-144 - Standard rail](#)

[19814601 - NS 35-144/2 - Standard rail](#)

[26241201 - DAE M12 - Pressure balance element](#)