



- NOTES:
1. INSERTION LOSS: 0.25 dB MAX.
 2. OPERATION TEMP: -40°C TO +80°C.
 3. MATERIALS:
 - ST2 ADAPTER:
 - BODY - ZINC ALLOY
 - RETENTION WASHER - BRASS, NICKEL PLATED
 - SLEEVE - CERAMIC, SINGLE-MODE
 - COPPER ALLOY, MULTI-MODE
 - DUST CAPS - PVC
 - NUT - COPPER ALLOY, NICKEL PLATED
 - LOCKWASHER - STEEL, NICKEL PLATED
 - FLANGE - ZINC ALLOY
 4. THIS PRODUCT IS RoHS COMPLIANT.

| PART NUMBER | ST2 ADAPTER SEE NOTE 3 | DUST CAP COLOR | FLANGE FINISH |
|-------------|---------------------------|-------------------|---------------|
| EHST2 | SINGLE-MODE | RED | NICKEL |
| EHST2M | DOUBLE-MODE | BLACK | NICKEL |
| EHST2B | SINGLE-MODE | RED | BLACK CHROME |
| EHST2MB | DOUBLE MODE | BLACK | BLACK CHROME |

CUSTOMER DRAWING

| | | | | | | | | | | |
|----------------------|------------|---------|----|------|--|-------|-------------|----------|---------------------|---------|
| | | | | | THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY. | | | | | |
| | | | | | SIZE | WIDTH | MULT | LBS/M | TEMPER | |
| | | | | | FINISH | | | MATERIAL | | |
| | | | | | SPEC No. | | | SPEC No. | | |
| | | | | | FIRST USED ON | | SCALE 1.5:1 | | | |
| B | 27621 | 12-4-15 | TO | TJK | DATE DRAWN | BY | CHKD | APVD | Switchcraft® | |
| A | 26306 | 12/1/08 | RS | TJK | 5/12/08 | JGK | RS | 6/2/09 | | 7/16/09 |
| REV | ECO NUMBER | DATE | BY | APVD | NAME | | | | SHEET 1 OF 1 | |
| REVISIONS | | | | | E SERIES ST2 FIBER OPTIC ADAPTER, RoHS | | | | PART No. | REV |
| DO NOT SCALE DRAWING | | | | | EHST2_SERIES | | | | B | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[EHST2M](#) [EHST2](#) [EHST2MB](#) [EHST2B](#)