


## Deep groove ball bearings, single row, shield on both sides



Principal dimensions			Basic load ratings		Fatigue load limit $P_u$	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
25	62	17	23,4	11,6	0,49	24000	13000	0,23	6305-2Z *



### Calculation factors

$k_r$  0,03  
 $f_0$  12