



Click [here](#) for the 3D model.

| Dimensions | |
|------------|---------------|
| D | 25mm +1mm |
| L | 58.5mm +/-2mm |

| Packaging Specifications | |
|--------------------------|--------------|
| Mounting | Bolt - M8x13 |
| Packaging | Bulk, Bag |
| Packaging Quantity | 162 |

| General Information | |
|---------------------|---|
| Series | C27 |
| Dielectric | Film/Foil Polypropylene |
| Style | Can |
| Description | Plastic Case and Cover, Ultra Sonically Welded Seal |
| Features | Ultra Sonically Welded Seal, Safety Class P0, UL_94 V0 Disk |
| RoHS | Yes |
| Termination | Tin Copper |
| Lead | BiPolar Cables |
| Qualifications | UL, VDE, UL (Construction Only), UL_94 V0 Disk |
| AEC-Q200 | No |
| Component Weight | 39.08 g |

| Specifications | |
|-----------------------|-----------|
| Capacitance | 1.5 uF |
| Capacitance Tolerance | 5% |
| Voltage AC | 470 VAC |
| Temperature Range | -25/+85°C |
| Rated Temperature | 85°C |
| Max dV/dt | 20 V/us |