

Specifications	Range
Measuring range	0~1250um
Accuracy	±(3%H+1)um
Resolution	0.1um (0~99.9um); 1um (100~1250um)
Measurement method	Single/Continuous
Measurement mode	Max/Min/Avg
Metal type	Ferrous/ non-ferrous
Features	
Display type	2.0-inches TFT LCD (320 x 240 pixels)
LCD brightness control	√
Auto rotatable screen	√
Unit conversion	√
Audio alarm	√
LED alarm	√
PC analysis software	√
USB communication	√
Quick test mode	√
Data storage	500 groups
Auto power off	√
Low battery indication	√
General Characteristics	
Power	3V battery (R03) x 2
Display	48mm x 36mm
Product color	Red and grey
Product net weight	175g
Product size	153.5mm x 64.5mm x 41mm
Standard accessories	Micro USB interface cable, standard piece, batteries, cloth bag
Standard individual packing	Gift box, English manual
Standard quantity per carton	20pcs
Standard carton	355mm x 320mm x 195mm

measurement	
Standard carton gross weight	7.5kg