

Specifications	UT692G
Measurement Range (dBm)	-50~+26
Wavelength Range (nm)	800-1700
Connector	Universal connector FC/SC/ST (FC as standard, SC and ST adapter as options)
Detector Type	InGaAs
Uncertainty	±5%
Calibrated Wavelength (nm)	850, 980, 1300, 1310, 1490, 1550, 1625, 1650
Display Resolution	Linear: 0.1%, logarithmic: 0.01dBm
Auto Power Off (min)	10
Power Supply	1. 5V AA alkaline battery (3 pcs)
Low Battery Indication	Low battery indication at about 3.3V, auto power off at about 3V
Battery Operation Time (h)	≥60
Drop Height (M)	2
Operating Temperature	0°C~40°C
Storage Temperature	-10°C~50°C
Dimensions (mm)	189×87×45
Net Weight (g)	286
Certification	CE, IP65,RoHS
General Characterisitics	
Power	1.5V battery x 3
Product color	Red and grey
Product net weight	286g
Product size	189mm x 87mm x 45mm
Standard accessories	1.5V Batteries, English manual, Dedicated pouch
Standard individual packing	gift box
Standard quantity per carton	10pcs
Standard carton measurement	295mm x 250mm x 210mm
Standard carton gross weight	14.5Kg (TBC)