

Specifications	LM70PRO
Display type	EBTN
Display size	2.4-inches
Range	70m
Min. display unit	0.001m
Measurement units	m/ft/in/ft+in
Measurement basis	Front/middle/rear
Accuracy	±2mm
Laser class	2
Laser type	630~670nm, < 1mW
Features	
Single measurement	√
Continuous measurement	√
Max/Min/Area	√
Volume/Pythagoras	√
Add/Subtract/Triangle area	√
Auto leveling horizontal/vertical	√
Electronic leveler	√
Data storage	20 groups
Auto laser off	30s without operation
Auto power off	√
Auto backlight off	√
Battery status display	√
USB charging	√
Tripod mounting hole	√
General Characterisitics	
Power	1.2V AAA recharge battery x 3
Product color	Red and grey
Product net weight	170g
Product size	59mm x 28mm x 137mm

Standard accessories	Carrying bag, USB interface cab
Standard individual packing	Gift box, English manual
Standard quantity per carton	20pcs
Standard carton measurement	390mm x 255mm x 345mm
Standard carton gross weight	8.3kg