


Bolt In Automotive Fuses



SPECIFICATIONS:

Bolt-In Mounting Configurations: Mounts on 8mm or less studs on 50.8mm centers.

Material: Copper terminals with UL Rated 94VO white thermoplastic housing

Applications: For high current (100A - 300A) applications on 48VDC or less systems requiring interrupting ratings up to 1000A.

For use with the Bussmann HMG Fuseholder - see page 21.

Time Current Specifications

Amp Rating	135% of I _N	200% of I _N	350% of I _N	600% of I _N	100% I _N Carry	Millivolt Drop @ 100% I _N	Interrupting Capability
100	120-1800 sec.	1-30 sec.	0.1-5 sec.	0.02-1 sec.	Min. 4 hrs.	Max. 150 mV	1KA @ 48VDC
125							
150							
175							
200							
250							
300							

PART NUMBERING SYSTEM

Series Rating

AMG - qq q

- 100 - 100 amps
- 125 - 125 amps
- 150 - 150 amps
- 175 - 175 amps
- 200 - 200 amps
- 250 - 250 amps
- 300 - 300 amps

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[AMG-100](#) [AMG-125](#) [AMG-175](#) [AMG-150](#) [AMG-250](#) [AMG-200](#) [AMG-300](#)