



M12 Connectivity

4 Port Distribution Box - 4 x M12, 5 pole (2 signals per port) with removable cap for self-wire home run cable

Stock No. 174-7830


Primary Features

LED indication for easy diagnostics


IP65, IP67 when leads inserted and tightened

Removable home run lead cap for easy installation and maintenance

UL and CSA approved













Wiring Schematic

174-7830





M12 Females 5-pole

Contact Layout

PIN 1	(+)
PIN 2	(NC)/(S2)
PIN 3	(-)
PIN 4	(NO)/(S1)
PIN 5	(Earth)
LED display	LED (green): Power / LED (yellow): (S1/S2)

Technical Data	
Operating voltage	24 V DC
Signal per port	2
Operating current per contact	max. 4 A
Connection	Spring clamp plug-in terminals: max. 1.5 mm ² (AWG 16)
Total current	max. 2 × 8 A
Housing	Plastic, flame retardant
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	Screw thread M12 × 1 mm
Temperature range	-20+80 °C
Dimensions H × W × D	100×50.2×17 mm