



## TECHNICAL SPECIFICATIONS

<b>Material:</b>	Zinc, Nickel plated
<b>Operating Temperature:</b>	-30°C to 90°C
<b>Attenuation Factor:</b>	>40 dB between 30 MHz and 1 GHz
<b>Cable Entry:</b>	Side
<b>Cable Diameter:</b>	Up to 13,0 mm
<b>Screening Test:</b>	SP Swedish National Testing and Research Institute
<b>Accessories:</b>	See page 40-43



### Features:

- Available in sizes 9-15-25-37
- Excellent EMI Shielding
- Cable sizes from 4,3 mm up to 13,0 mm
- Re-openable
- Strain relief inserts ensure a secure termination



Size MHDVSL	Dim A	Dim B	Dim C
9-way	14,5	36,3	31,0
15-way	14,5	40,3	39,5
25-way	14,5	40,3	53,2
37-way	14,5	40,3	69,7

### Order Code

**MHDVSL - XX - B - K**

Series: \_\_\_\_\_

Size (xx): 9,15,25, 37 \_\_\_\_\_

Plating Select: \_\_\_\_\_

Omit = Nickel, B = Black Chromate

Packing Style: \_\_\_\_\_

K = Individual Kit, Omit = Bulk

