



ENGLISH

Datasheet

RS Pro Swivel Plate Castor, 50kg

RS Stock No: **712-4869**



Product Details

RS Pro swivel castor has load capacity of 50 kg. It features anti-static rubber tyre for non-marking floor surface.

Features and Benefits

- Grey anti-static rubber tyres
- Chrome plated forks
- Light to medium duty applications
- Swivel castors fitted with double ball race in swivel head



ENGLISH

Specifications:

Features	Anti-Static
Fixing Centres (Length)	50 mm
Fixing Centres (Width)	36 mm
Fixing Centres	50 x 36 mm
Fixing Hole Size	6.5 mm
Fixing Plate Dimensions	65 x 50 mm
Fixing Plate Length	65 mm
Fixing Plate Width	50 mm
Hub Bearing Type	Plain Bore
Hub Material	Rubber
Includes Brake	Yes
Load Capacity	50 kg
Number of Fixing Holes	4
Overall Height	109 mm
Rotation	Swivel
Tyre Material	Rubber
Weight Class	Light Duty, Medium Duty
Wheel Diameter	80 mm
Wheel Width	20 mm