

# TORQUE WRENCH 3/4 INCH DRIVE 450NM

Item ID: 3492AG-E



- 3/4" drive torque wrench covering 65-450Nm
- Equipped with an in-built angular gauge for easier after tightening of stretch bolts (TTY torque to yield fasteners)
- Click type mechanism with easily recognisable signal when the required torque is reached
- Simple to adjust and easy to read Nm scale
- Additional ft/lb reference scale (range 48-330 ft/lb)
- Clearly marked with three bands to show the correct place on the handle where pressure should be applied to give a more accurate torque reading
- Twist locking facility to ensure the set torque is maintained
- Reversible 24 teeth ratchet mechanism (DIN3122) giving 15° increments for strength and for added reference when torqueing stretch bolts
- Designed to torque right hand (clockwise) fasteners
- Accurate to +/- 4% and conforms to ISO6789 for assured reliability and accuracy
- Individually tested and certified at the time of manufacture
- Each torque wrench has it's own individual certification number for easier quality control management
- Supplied in a handy storage case

<u>Length (mm):</u>	<u>167</u>
<u>Width (mm):</u>	<u>1297</u>
<u>Height (mm):</u>	<u>133</u>
<u>Weight (kg):</u>	<u>5.486</u>

*Technical changes and errors may occur*

**WWW.TENGOOLS.COM**



*Get organised™*