

# PANEL MOUNT INDICATOR, NON-RELAMPABLE

## LED TECHNOLOGY

MOUNTING HOLE, Ø 0.500"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
<b>LED 12V SERIES</b>				
WL-1091QM1-12V	RED	12V-14V	20mA	100,000
WL-1091QM5-12V	GREEN	12V-14V	20mA	100,000
WL-1091QM7-12V	YELLOW	12V-14V	20mA	100,000
<b>LED 24V SERIES</b>				
WL-1091QM1-24V	RED	24V-28V	20mA	100,000
WL-1091QM5-24V	GREEN	24V-28V	20mA	100,000
WL-1091QM7-24V	YELLOW	24V-28V	20mA	100,000

## NOTES

1. Recommended panel thickness  
0.030" to 0.090"
2. .187" terminals are standard
3. Storage temperature  
 $T_{STG}$ : -25°C - +80°C
4. Ambient temperature  
 $T_A$ : -20°C - +60°C
5. DC operation only
6. Voltage tolerance  
 $V_{OP}$ : ±10%
7. Body material  
Nylon, white
8. Lens material  
Polycarbonate
9. Bezel material  
Stainless steel
10. Anode (+)  
Marked above terminal
11. .250 quick connects  
available upon request


## CERTIFICATIONS

UL (E340667), RoHS



**RoHS**  
COMPLIANT

## DIMENSIONAL CHARACTERISTICS



## OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

**wamco**  
LIGHTING

P: (714) 545-5560 F: (714) 545-6093

W: WWW.WAMCOINC.COM E: INFO@WAMCOINC.COM

WL-1091QMx-xxx Series Rev 5