



House service fuse-link, low voltage, 100 A, AC 415 V, 33 kA, BS system C type II, 30 x 57 mm, gL/gG, BS



Part no. **100A 415V AC H/SERVICE**
 Catalog No. **100LR85**

Delivery program

Product range			Fuse
Basic function			House service fuse-link
Field of application			low voltage
Rated current	I	A	100
Rated voltage			AC 415 V
Construction size			BS system C type II
Size			30 x 57 mm
Utilization category			gL/gG
Breaking Capacity		kA	33
usable for size/applications			protection of incoming cables into residential and commercial properties
Standard/Approval			BS
Shape			cylindrical
Standards/Regulations			BS88-3

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss10.0.1-27-14-20-02 [AFZ797013])			
Size			Other
Rated voltage		V	415 - 415
Rated voltage			Other
Voltage type			AC
Utilization category			gL/gG (cable protection/equipment protection)
Rated operating frequency		Hz	45 - 62
Nominal current		A	100
With striker			No
Release characteristic			Other
Breaking capacity		kA	33