

Specifications	Range	Accuracy
IRT Temperature	-40~0°C/-40~32°F	±4°C/ ±7.2°F
	0~400°C	±(1.5%+2°C)
	32~752°F	±(1.5%+3.6°F)
	400~800°C	±(2.0%+2°C)
	752~1472°F	±(2.0%+3.6°F)
K-Type Temperature	-40°C~1080°C	±(1.5%+3°C)
	-40°F~1976°F	±(1.5%+5.4°F)
Resolution	<199>	0.1°C/0.1°F
	>199.9	1°C/1°F
Repeatability		±0.1°C
Emissivity		0.10~1.00
Optical Resolution		12:01