


# solenoid coil VACF-A-A1-3W

Part number: 8030828

FESTO



## Data sheet

Feature	Value
Assembly position	Any
Duty cycle	100%
Insulation class	H
Characteristic coil data	230/240 V AC: 50/60 Hz, pick-up power 3.9 VA, holding power 2.8 VA
Permissible voltage fluctuation	+/- 10 %
Certificate issuing department	DNVGL-TAA000011J
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Protection class	IP65
Ambient temperature	-20 ... 50 °C
Maritime classification	see certificate
Electrical connection	to EN 175301-803 Plug pattern type A to EN 175301-803
Mounting type	With knurled nut
Materials note	Conforms to RoHS
Material housing	PA Steel
Material solenoid coil	Copper Steel Thermoplastic
Material winding	Copper