

ASSMANN DVI Adapter

AK-320502-000-S
EAN 4016032300496



DVI adapter, DVI(24+1) - DVI(24+5) M/F, DVI-D dual link, bl

This adapter is suitable to connect a DVI(24+5) cable to device or cables with DVI(24+1) connector, for example .

Full HD, Dual-Link

- Support 2560 x 1600 pixel with 30Hz
- Connector 1: DVI-D, (24+1), plug
- Connector 2: DVI-I, (24+5), jack
- Cable type: Dual-Link

- Hoods: molded
- Shielding: single shielding
- Connector surface: nickel-plated
- HDTV Resolution max.: 2560 x 1600 Pixel, 60Hz
- Color connector: black
- Packaging: Polybag
- Assortment: DVI Cables
- HDTV Standard: Full HD

Logistische Daten

	Anzahl (Stück)	Gewicht (kg)	Tiefe (cm)	Breite (cm)	Höhe (cm)	cm ³
Karton-VPE	200	8,20	37,00	24,00	18,00	15.984,00
Innen-VPE	10	0,41	27,00	24,00	2,00	1.296,00
Einzel-VPE	1	0,04	8,00	5,00	1,50	60,00
Netto einzeln ohne VP	1	0,04	8,00	5,00	1,50	60,00



Weitere Anwendungsbilder:

