


Specifications:  
 Current rating:0.5A AC/DC.  
 Voltage rating:40V AC/DC  
 Contact resistance:30m ohm Max.  
 Insulation resistance: 100M ohm. Min.  
 Withstanding voltage:300V AC/minute.  
 Operating temperature range:-20°C~+85°C

Material:  
 Insulator:High Temp. Plastic(UL94V-0)  
 Insulator Color:Black  
 Contact:Copper Alloy  
 Plated:Gold Plated on Contact Area,  
 Tin Plated on Solder Tails.  
 Shell:Steel & Copper Alloy, Nickel Plated



PCB Layout

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.25 .XX=±0.15	<h1 style="color: red; text-align: center;">CnC Tech</h1> <p style="text-align: center;">Industrial Cable and Connector Technology</p>	
				CHECKED:	UNIT: MM		
					SCALE:1:1	HDMI Receptacle R/A Dip Type	SIZE
	05-FEB-2020			APPROVAL:	SHEET: 1 / 2	PART NO:	A4
REV	DATE	FILE	BY		PROJECTION:	2000-1-1-20-00-BK	