


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2021-06-01	Sam Ho	Rev.02 to A, Initial Released



MSXS-XXBMMM-PL8XXX

XX: 01~99Meters
 01: 01Meter
 02: 02Meters
 :
 99: 99Meters

XX: No. Of Pin

- Note:
- * \varnothing Important Dimension
 - * Waterproof Rate: IPX8, Mated 1m/24h
 - * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper Alloy, Gold Plated
 - Shield & Shell & Spring: Matel
 - Nut: Thermoplastic, Black
 - Outer Mold: Thermoplastic, Black
 - * Cable: CAT-6A, 26#*4P+AL/MY+B, TPU Jacket, OD 6.8mm, GN.
 - * Cable Length Tolerance:
 - 1M < L ≤ 3M: +50/-0 mm
 - 3M < L ≤ 5M: +100/-0 mm
 - 5M < L ≤ 10M: ±100 mm
 - 10M < L ≤ 20M: ±200 mm
 - 20M < L ≤ 30M: ±300 mm
 - 30M < L ≤ 99M: ±500 mm

Conn.	<p>8P</p>	Shield	Braid	編織	Twist
		8	Blue	藍	
		7	White/Blue	白/藍	
		6	Brown	棕	
		5	White/Brown	白/棕	
		4	Green	綠	
		3	White/Green	白/綠	
		2	Orange	橘	
1	White/Orange	白/橘			
Pin Assignment Front View		Conn.	Wire Color		Pin Out

UNIT:mm		TITLE N SEN, M12 X -SHLD, 08P, PUSH PULL CABLE W/O SR, M, M, MOLDING	
TOLERANCE ±0.50mm	SCALE 2:1	SIZE A4	SHEET 1 OF 1
REV. A	WC-REV.	\varnothing : Inspection item	

Amphenol LTW		ITEM NO	DRAWN BY	DATE
安費諾亮泰企業股份有限公司		DWG NO MSXS-XXBMMM-PL8XXX	Sam Ho	2021-04-09
		CUSTOMER ALTW	CHECKED BY Fred Lee	DATE 2021-04-09
			APPROVED BY Fred Lee	DATE 2021-04-09