







Number of contacts

8

5 A 50 V 0.8 kV 3
+ shielding

Han
HMC

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
Han-Modular®, Adapter module, Han® Gigabit module, Han® Shielded module, Han® Megabit module 		09 14 001 3011	09 14 001 3111	
Han® Gigabit HMC insert, Crimp termination, Cat. 6A  Please order crimp contacts separately. Please order adapter module separately.	0.09 ... 0.52	09 14 208 3011	09 14 208 3111	 Cable outer diameter ≤ 14 mm
Han® Gigabit HMC insert, Crimp termination, Cat. 6A  With additional shield connection to the hinged frame Please order crimp contacts separately. Please order adapter module separately.	0.09 ... 0.52	09 14 208 3012	09 14 208 3112	 Cable outer diameter ≤ 14 mm