

1

2

3

4

5




6

7

A

A

P1



P2

PIN ASSIGNMENT	
P1	P2
1 _____	1
2 _____	2
3 _____	3
4 _____	4
SHEEL _____	SHEEL

B

B

C

C

D


D

E

E

F

F



1PC/PE BAG

- ① Electronic Test:
- 1.100% Test,(Open,Short,Miss Wire)
 - 2.Contact Resistance:3 ohm max.
 - 3.Insulation Resistance:20M ohm min.
 - 4.Hi-Pot:300V DC/10ms
 - 5.Voltage Rating: 30V
 - 4.Current Rating: 1.5A
- ① Mechanical:
- 1.Mating force: 3.57Kgf max
 - 2.Unmating force: 1.02Kgf min
 - 3.Operating temperature: -5°C~60°C

Packaging: PE bag

⑥	PE BAG	1/10	CLEAR SIZE:170*250*0.05mm PRINT BLACK"MADE IN CHINA" + "10PCS".
⑤	PE BAG	1	CLEAR SIZE:80*100*0.05mm PRINT BLACK"MADE IN CHINA"+ "1PC".
④	OUT JACKET	6g	BEIGE(IV-29) 40P PVC (WM-006)
	IN JACKET	4g	CLEAR LDPE (NM-009)
③	CABLE	5	UL1007 28AWG L=30MM
②	CONN	1	USB A FEMALE,SHELL NICKEL PLATING MATERIAL STEEL, PIN GOLD FLASH PLATING MATERIAL BRASS SHORT BODY
①	CONN	1	USB B FEMALE,SHELL NICKEL PLATING MATERIAL STEEL, PIN GOLD FLASH PLATING MATERIAL BRASS SHORT BODY
NO.	NAME	Q'TY	SPECIFICATION

RoHS compliant
Unit: mm

Scale	Free				Date	Name	Customer-No.
TOLERANCE					Drawn	20.02.2017	Amy
					Approved	29.11.2019	Carson
							ASSMANN WSW-No.
							A-USB-2
DIM	TOL	①	Update	29.11.2019	Carson	Drawing-No.	
		②	Drawn	20.02.2017	Amy	ASS 7876 CA	rev01
Angle	TOL	Id.	Modification	Date	Name	Replace	Sheet



1

2

3

4

5

6

7

H

H