

FEATURES

- Features a 28.2 mm diameter float
- Rugged and durable
- Float switch can operate within water, acids and oil
- Suitable for food contact

RS PRO Vertical Float Switch, Stainless Steel, NO/NC, Float, 300mm, 250V, 200V

RS Stock No.: 762-1036



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO, this 304 Stainless Steel vertical float switch operates at 230 V ac. It has an N/O (normally open) configuration. It features a 28.2 mm diameter float that is rugged and durable. With an extensive operating temperature range of -40 °C to +125 °C, this float switch can operate within water, acids and oil. It is also suitable for food contact.

General Specifications

Device Type	Float
Switch Output	NO/NC
Body Material	Stainless Steel
Applications	Control a pump, as an indicator, an alarm

Electrical Specifications

Maximum AC Voltage	250V
Maximum DC Voltage	200V
Maximum Current	2A
Current Rating	1.5A

Mechanical Specifications

Mounting Type	Vertical
Cable Length	300mm

Operation Environment Specifications

Minimum Operating Temperature	-40°C
Maximum Operating Temperature	125°C

Approvals

Compliance/Certifications	RoHS Certificate Of Compliance
---------------------------	--------------------------------

