

3AG Normal-Blo Fuse

3AG (311) series Normal-Blo fuses are for use in radios, amplifiers, etc. Features straight type fuse element positioned to center of fuse for easy identification of blown fuse.

Voltage Rating: 32V.

US & Canadian Boxed No.	US Carded No.	Voltage Rating	Description
V 311005	311005 BP	32V	5A 3AG Normal-Blo
V 311010	311010 BP	32V	10A 3AG Normal-Blo
V 311015	311015 BP	32V	15A 3AG Normal-Blo
V 311025	311025 BP	32V	20A 3AG Normal-Blo

8AG Normal-Blo Fuse

8AG (362) series Normal-Blo fuses are smaller in size ($\frac{1}{4}$ " x 1") and are designed to be used where space limitations prevent the use of 3AG fuses.

Voltage Rating: 32V.

Approvals: UL listed: $\frac{1}{8}$ – 5A, CSA Certified: $\frac{1}{4}$ – 5A.

US & Canadian Boxed No.	US Carded No.	Voltage Rating	Description
V 362002	362002 BP	32V	2A 8AG Normal-Blo
V 362005	362005 BP	32V	5A 8AG Normal-Blo

3AB Fast-Acting & Slo-Blo® Ceramic Fuse

Ceramic body construction permits higher interrupting and voltage ratings. Ideal for applications where high current loads are expected.

Voltage Rating: 250V ($\frac{1}{8}$ – 20A), 125V (25 – 30A).

Approvals: UL listed and CSA Certified: $\frac{1}{8}$ – 15A, Recognized under the Components Program of UL: 20 – 30A.

US & Canadian Boxed No.	US Carded No.	Voltage Rating	Description
V 314010	314010 BP	250V	10A 3AB Fast-Acting
V 314015	314015 BP	250V	15A 3AB Fast-Acting
V 314020	314020 BP	250V	20A 3AB Fast-Acting
V 326015	326015 BP	250V	15A 3AB Slo-Blo

3AG Shock-Safe Panel Fuseholders

Designed to eliminate the possibility of electrical shock, as defined in IEC standards 65 and 257. Shock-Safe fuseholders feature a low profile body, finger-grip knob and anti-tease feature that eliminates circuit interruption when knob is accidentally depressed.

Voltage Rating: 250V.

Approvals: UL listed and CSA Certified. Recognized under the Components Program of UL.

US & Canadian Boxed No.	US Carded No.	Canadian Carded No.	Amp Rating (Max)	Description
3453LF8A	3453LF8C	3453LF8CA	20A	with $\frac{1}{4}$ " straight NEMA/DIN Quick Connect Terminal
3453LF2A	3453LF2C	3453LF2CA	20A	with $\frac{3}{16}$ " straight dual purpose solder terminal
346877	346877C	346877CA	15A	Flip top 3AG Fuseholder
348877	348877C	348877CA	15A	Low profile Snap Mount 3AG Fuseholder

FUSES



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[03453LF2X](#) [03453LF8X](#) [03480877Z](#) [03453LF2XP](#) [03453LF8XP](#)