

Recommended P.C.B. Layout
Layout Tolerance = ± 0.05 mm

NOTE:

- MATERIAL,
HOUSING: HIGH TEMP PLASTIC, UL94-V0
TERMINAL: COPPER ALLOY, T=0.15MM
CAP: STAINLESS STEEL, T=0.1MM
- FINISH:
TERMINAL: GOLD AT CONTACT,
G/F OVER 1.27um (50u")MIN Ni OVER ALL
- SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1420
- THE HSG. WILL WITHSTAND EXPOSURE TO 260C PEAK TEMP. FOR 10 SEC. IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- PRODUCT NUMBERING:
20021321 - 0 0 0 XX X X LF




LEAD FREE
PLATING:
1: GOLD FLASH, ALL OVER
4: 0.25um(10U")GOLD AT CONTACT
8: 0.76um(30U")GOLD AT CONTACT
PACKING
D: TUBE+ CAP
T: TUBE
C: REEL+CAP(6,8,10,12,16,20P)
PIN COUNT
6,8,10,12, ,,,,,, 98, A0
(EVERY EVEN PIN)
SELECTED LOADED OPTION
0: FULLY LOADED
1: SEE TABLE 1

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c.FCI. Droits de reproduction FCI.






All rights strictly reserved. Reproduction or issue to third parties in any form whatsoever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ± 0.38		projection		title		
A	T09-1117	S.LIN	09/15/09		.XX ± 0.25				1.27X1.27MM BTB, RECEPTACLE SMT		
B	T10-0019	S.LIN	01/20/10	angles	.XXX ± 0.10		MM		product family 585		
C	T10-0061	S.LIN	10'-5-07		0° ± 2'				code TWN		
D	T10-0173	S.LIN	10'-10-22	dr	STERLING LIN	09/15/09	← MM →	scale	size		sheet
				engr	STERLING LIN	09/15/09	NA		A4		
				chr	GARY HSIEH	09/15/09				1 of 2	
				appd	JOSEPH HSIA	09/15/09					
sheet index	revision sheet	D	D								
		1	2								



P/N: 20021321-00108D4LF



P/N: 20021321-00214D4LF

DASH No.	DIM	Amount of Pins	PIN REMOVED	PIN FILLED
-001 08 D4 LF		7	-	#4
-002 14 D4 LF		13	-	#2

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ± 0.38		projection	title			
A	T09-1117	S.LIN	09/15/09		.XX ± 0.25			1.27X1.27MM BTB, RECEPTACLE SMT			
B	T10-0019	S.LIN	01/20/10	angles	.XXX ± 0.10			product family 585			
C	T10-0061	S.LIN	10'-5-07		0° ± 2°			code TWN			
D	T10-0173	S.LIN	10'-10-22	dr	STERLING LIN	09/15/09	MM	size		sheet	
				engr	STERLING LIN	09/15/09		20021321		2 of 2	
				chr	GARY HSIEH	09/15/09	scale NA	A4			
				appd	JOSEPH HSIA	09/15/09					
sheet index	revision sheet	D	D								
		1	2								

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c.FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatsoever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.