


REVISIONS		REVISED BY	DATE	APPR
SYM	DESCRIPTION			

PART NO.	THREAD	STANDOFF		
		"A" ±.015	"B"	"C"
4375	4-40	.250	3/16"	3/16"
4376	6-32	.250	1/4"	.21
4377	8-32	.250	3/8"	.21
4378	4-40	.375	3/16"	3/16"
4379	6-32	.375	1/4"	1/4"
4380	8-32	.375	3/8"	.21
4381	4-40	.500	3/16"	3/16"
4382	6-32	.500	1/4"	1/4"
4383	8-32	.500	3/8"	3/8"
4384	4-40	.625	3/16"	3/16"
4385	6-32	.625	1/4"	1/4"
4386	8-32	.625	3/8"	3/8"
4387	4-40	.750	3/16"	3/16"
4388	6-32	.750	1/4"	1/4"
4389	8-32	.750	3/8"	3/8"
4390	4-40	.875	3/16"	3/16"
4391	6-32	.875	1/4"	1/4"
4392	8-32	.875	3/8"	3/8"
4393	4-40	1.000	3/16"	3/16"
4394	6-32	1.000	1/4"	1/4"
4395	8-32	1.000	3/8"	3/8"
4396	4-40	1.125	3/16"	3/16"
4397	6-32	1.125	1/4"	1/4"
4398	8-32	1.125	3/8"	3/8"
4399	4-40	1.250	3/16"	3/16"
4400	6-32	1.250	1/4"	1/4"
4401	8-32	1.250	3/8"	3/8"
4402	4-40	1.375	3/16"	3/16"
4403	6-32	1.375	1/4"	1/4"
4404	8-32	1.375	3/8"	3/8"
4405	4-40	1.500	3/16"	3/16"
4406	6-32	1.500	1/4"	1/4"
4407	8-32	1.500	3/8"	3/8"
4408	4-40	1.625	3/16"	3/16"
4409	6-32	1.625	1/4"	1/4"
4410	8-32	1.625	3/8"	3/8"
4411	4-40	1.750	3/16"	3/16"
4412	6-32	1.750	1/4"	1/4"
4413	8-32	1.750	3/8"	3/8"
4414	4-40	2.000	3/16"	3/16"
4415	6-32	2.000	1/4"	1/4"
4416	8-32	2.000	3/8"	3/8"



MATERIAL	NYLON 6/6 U194V2	FINISH	NATURAL
DIMENSIONAL TOLERANCES	UNLESS OTHERWISE SPECIFIED		
XX	.XXX	XXX	.XXX
---	---	---	---
FRACTIONS	ANGLES	SCALE	4:1
HEAT TREAT	---	DRAWN: J. TEASDALE	DATE 4-6-94
PLOT SCALE	1=1	CHECKED: ED. MCKINNEY	DATE 4-6-94
		APPROVED: (SEE ABOVE)	DATE 4-11-95

TITLE	4375 THRU 4416
1/4 HEX NYLON MALE/FEMALE STANDOFF	

ABBATRON	Electronic Connectors and Hardware	632 Arch Street, Meadville, Pa. 16335
SIZE	DRAWING NUMBER	ISSUE
B	SD: SMP-00271	C