
solenoid valve VUVS-L25-B52-D-G14-F8-1B2 Part number: 575520





Data sheet

Feature	Value
Valve function	5/2 bistable
Type of actuation	electrical
Valve size	26.5 mm
Standard nominal flow rate	1,300 l/min
Operating pressure	1.5 10 bar
Design structure	Piston slide
Authorisation	c UL us - Recognized (OL)
Certificate issuing department	DNVGL-TAA000011J
Protection class	IP65
	with plug socket
	to IEC 60529
Nominal size	6.9 mm
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Manual override	detenting
	Pushing
Type of piloting	Piloted
Pilot air supply	Internal
Flow direction	non reversible
Overlap	Positive overlap
b value	0.4
C value	5.6 l/sbar
Switching time reversal	11 ms
Duty cycle	100 %
Max. positive test pulse with logic 0	2,000 μs
Max. negative test pulse with logic 1	3,600 μs
Characteristic coil data	24 V DC: 3.3 W
Permissible voltage fluctuation	+/- 10 %
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Vibration resistance	Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	-10 60 °C
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Ambient temperature	-10 60 °C
Product weight	428 g
Electrical connection	Plug pattern type B to EN 175301-803
Mounting type	Optional
	on manifold rail
	with through hole
Scavenging orifice connection	Non-ducted



Feature	Value
Pilot exhaust port 82	M5
Pilot exhaust port 84	M5
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Pneumatic connection, port 3	G1/4
Pneumatic connection, port 4	G1/4
Pneumatic connection, port 5	G1/4
Materials note	Conforms to RoHS
Material seals	HNBR
	NBR
Material housing	Aluminium die cast
	Painted
Material Piston slide	Wrought Aluminium alloy
Material screws	Galvanised steel