

ABBATRON

Premier Supplier of Electronic Hardware


HH Smith

Custom Capabilities | Test Accessories | Plugs, Jacks, Posts | Connectors | Hardware | Spacers/Standoffs

- [Home](#)
- [About](#)
- [Abbatron](#)
- [Products](#)
- [Locate](#)
- [Distributor](#)
- [or](#)
- [Representative](#)
- [Contact Us](#)
- [Request](#)
- [Information](#)
- [Site Map](#)

Brass Male/Female Hex Standoffs

- Hex shaped standoffs are ideal wherever wrench tightening may be required.
- Standard Nickel Plating provides a hard, bright, non-oxidizing surface which will stand up to difficult ambient conditions.



BODY LENGTH		4-40	6-32	8-32
.250	1/4	8216	8248	8280
.375	3/8	8217	8249	8281
.500	1/2	8218	8250	8282
.625	5/8	8219	8251	8283
.750	3/4	8220	8252	8284
.875	7/8	8221	8253	8285
1.000	1	8222	8254	8286
1.125	1-1/8	8223	8255	8287
1.250	1-1/4	8224	8256	8288
1.375	1-3/8	8225	8257	8289
1.500	1-1/2	8226	8258	8290
1.625	1-5/8	8227	8259	8291
1.750	1-3/4	8228	8260	8292
2.000	2	8229	8261	8293
2.500	2-1/2	8230	8262	8294
3.000	3	8231	8263	8295

Inventory Search

Cross Reference

UPS Tracking

632 Arch Street, POB
726 Meadville, PA 16335
USA 814-724-6440

[Contact Webmaster](#)

© June 6, 2005

Thread Specs for Male/Female Spacers			
Thread Size	Body Length	Thread Depth	Thread Length
4-40	1/4 to 3/8	3/16	7/32
6-32	1/4 to 3/8	3/16	9/32
	1/2 to 3"	3/8	9/32
8-32	1/4 to 3/8	3/16	13/32
	1/2 to 3"	7/16	13/32

[home](#) | [about abbatron](#) | [products](#) | [locate distributor or representative](#) | [contact us](#) | [request information](#) | [site map](#)