

Specification	Range	UT890C
DC Voltage	600mV/6V/60V/600V/1000V	±(0.5%+2)
AC Voltage	6V/60V/600V/750V	±(0.8%+3)
ACV Frequency	10Hz ~ 10kHz	± ( 0.1%+5)
DC Current	60uA//600uA/6mA/60mA/600mA/20A	±(0.8%+8)
AC Current	60uA/600uA/6mA/60mA/600mA/20A	±(1%+12)
Resistance	600Ω/6kΩ/60kΩ/600kΩ/6MΩ/60MΩ	±(0.8%+3)
Capacitor	6.000nF/60.00nF/600.0nF/6.000μF/60.00μF/600.0μF/6.000mF/60.00mF/100.0mF	±(3%+10)
Frequency	9.999Hz ~ 9.999MHz	±(1.0%+5)
Temperatue	-40°C ~ 1000°C/-40°F ~ 1832°F	±(1.5%+5)
<b>Fetures</b>		
Display Count		6000
Manual Range		√
NCV		√
hFE		√
Diode Test		√
Continuity Test		√
True RMS		√

Fuse blowing alarm		√
Acousto-optic indication(N CV/continuity)		√
High voltage false detection	1000Vrms	√
Current (AC/DC) mode memory		√
Over-current alarm	≥20A	√
Low Battery Indication	≤2.5V	√
Data Hold		√
REL		√
Max/Min	V、A	√
Auto Power Off	15Min	√
Back light	30s	√
Operation Temperature	0°C ~ 40°C	
Safety	CAT II 1000V/CAT III 600V	
<b>General Characteristics</b>		
Power	1.5V x 2	
Product color	Red and Gray	
Product Net Weight	346g	
Product Size	183mm x 88mm x 56mm	
Standard Individual Packing	Gift Box, Manual	

Standard Quantity Per Carton	40pcs
Standard carton measurement	690mm x 450mm x 340mm
Standard carton gross weight	23Kg