

Specifications	Range	UT123
DC Voltage	4V/40V/400V/600V	± ( 0.5% + 2 )
AC Voltage	4V/40V/400V/600V	±(1.0%+3)
Resistance	400Ω/4kΩ/40kΩ/400kΩ/ 4MΩ/20MΩ	±(0.8%+2)
Temperatue	-40°C ~ 300°C/-40°F ~ 572°F	±4°C
<b>Features</b>		
Display Count		4000
Autol Range		√
NCV		√
Continuity Test		√
Acousto-optic indication(NCV/continuity/battery power)		√
Low Battery Indication	≤2.7V	√
Data Hold		√
Auto Power Off	15Min	√
Operation Temperature		0°C ~ 40°C
Safety		CAT III 600V
<b>General Characteristics</b>		
Power	1.5V battery (R03) x 2	
Display	44mm × 26mm	
Product color	Red and grey	

Product net weight	130g
Product size	130mm x 65m x 28mm
Standard accessories	Batteries, Thermocouple
Standard individual packing	Gift Box, Manual
Standard quantity per carton	60pcs
Standard carton measurement	480mm x 340mm x 325mm
Standard carton gross weight	15.5kg