



SPECIFICATION

1. Rated Voltage.....12Vp-p
2. Max Rated Input Voltage.....30Vp-p
3. Resonant Frequency25±3kHz
4. Rated Frequency Range.....2.5~50KHz
5. Min Rated SPL.....90dB at 12Vp-p/3.7-7KHz/50cm
Min Rated SPL.....90dB at 12Vp-p/20-25KHz/50cm
6. Case Material.....PC/Black
7. Operating Temperature.....-20-+60(°C)
8. Storage Temperature-30-+70(°C)



				NINGBO VOISE ELECTRONICS CO.,LTD http://www.nbvoise.com	
No.	DESCRIPTION	APPROVED	DATE	Tweeter VCT4112	
TOLERANCES UNLESS NOTED OTHERWISE .X ± .XX ± .XXX ± 90° FORMED +2° ANGLES -1°		APPROVALS	DATE		
FIRST ANGLE PROJECTION 		DRAWN		UNIT	DWG NO.
		CHECKED		mm	VS20190715015
		APPROVED	19.07.15	SCALE	SHEET
					VER 1.0