



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT4S	.06 (1.5)	4.00 (102)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	14.5 (368)	50 (222)	STANDARD	CURVED	.56 (254)
PLT4.5S	.06 (1.5)	4.50 (114)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	15.5 (394)	50 (222)	STANDARD	CURVED	.57 (257)
PLT5S	.06 (1.5)	5.00 (127)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	17.5 (445)	50 (222)	STANDARD	CURVED	.65 (293)
PLT6LH	.188 (4.8)	6.00 (152)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	21.9 (556)	120 (534)	LIGHT HEAVY	STRAIGHT	1.86 (845)
PLT7LH	.188 (4.8)	7.00 (178)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	24.7 (627)	120 (534)	LIGHT HEAVY	STRAIGHT	2.09 (950)
PLT8LH	.188 (4.8)	8.00 (203)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	27.6 (701)	120 (534)	LIGHT HEAVY	STRAIGHT	2.32 (1054)
PLT9LH	.188 (4.8)	9.00 (229)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	30.5 (775)	120 (534)	LIGHT HEAVY	STRAIGHT	2.56 (1161)
PLT10LH	.188 (4.8)	10.31 (262)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	34.3 (871)	120 (534)	LIGHT HEAVY	STRAIGHT	2.83 (1285)

NOTES:
 *SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL:
							PAN-TY CABLE TIES - PLT SERIES	
							CUSTOMER DRAWING	
							ITEM REVISION NAME W10001CC/27	PANDUIT
							DATASET FILE NAME W10001CC/27-SS-5540 SHEET 3 CUSTOMER	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	NYLON 6.6
							.x ± .02 [.5] .xxx ± .020 [.51] ANGLES ±	
27	4/07/14	BWG	MPH	JADE	REVISED NOTE.	SS-5540/27	THIRD ANGLE PROJECTION	DRAWING NUMBER: SS-5540 SHEET 3
26	8/13/13	BWG	KJM	RTFI	UPDATED TITLE BORDER.	SS-5540/26		
							DRAWN BY CEW	
							DATE 12-27-84	
							CHK HVP	
							SCALE NONE	
								SHT 1 OF 1
								SIZE A

D10100DA/16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PLT6LH-C](#) [PLT8LH-L](#) [PLT8LH-C](#) [PLT4S-C](#) [PLT4S-C0](#) [PLT6LH-L0](#) [PLT6LH-C0](#) [PLT10LH-L](#) [PLT7LH-L](#)
[PLT10LH-C](#) [PLT4.5S-C0](#) [PLT4S-C10](#) [PLT4S-M20](#) [PLT4S-M30](#) [PLT5S-C](#) [PLT5S-M0](#) [PLT5S-M2](#) [PLT7LH-C30](#)
[PLT9LH-C0](#) [PLT4S-C30](#) [PLT4S-M14](#) [PLT4S-M2](#) [PLT4S-M1](#) [PLT4S-C6](#) [PLT4S-M8](#) [PLT4S-C4Y](#) [PLT5S-M4Y](#)
[PLT4S-C20](#) [PLT5S-M6](#) [PLT8LH-Q0](#) [PLT4S-C8](#) [PLT5S-M5](#) [PLT4.5S-M0](#) [PLT9LH-C300](#)