



NOTES:

1. THIS PRODUCT IS RoHS COMPLIANT
2. MATERIALS:
HOUSING AND COVER: HIGH GRADE THERMOPLASTIC, UL94V-0 RATED, COLOR BLACK;
CENTER PIN: BRASS, NICKEL PLATED PER QQ-N-290, CLASS 1;
PIN AND SHUNT TERMINALS: BRASS, SILVER PLATED PER QQ-S-365,
SLEEVE SPRING: SPRING COPPER ALLOY, SILVER PLATED PER QQ-S-365,

3. SPECIFICATIONS:
LIFE: 5000 CYCLES;
INSERTION FORCE: 5 LB [2.3 KG] MAX;
WITHDRAWAL FORCE: 0.5 LB [0.2 KG] MIN;
CONTACT RESISTANCE: 30 MILLIOHM MAX, 60 MILLIOHM MAX. AFTER TEST;
INSULATION RESISTANCE: 30 MEGAOHM MIN. @ 100VDC;
DIELECTRIC WITHSTANDING VOLTAGE: 250VAC FOR 1 MINUTE;
CURRENT (CARRYING): 5A

REV	ECO NUMBER	DATE	BY	APVD
A	25129	8-29-05	JL	MW
REVISIONS				

★ STAR SYMBOL DENOTES CRITICAL DIMENSION

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES
- TWO PLACE DECIMALS ±0.01
- THREE PLACE DECIMALS ±0.005
- ANGLES ±1°
- ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.
2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002
3. REMOVE ALL BURRS

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE	WIDTH	MULT	LBS/M	TEMPER					
FINISH					MATERIAL				
SPEC No.					SPEC No.				
FIRST USED ON					SCALE				
					4:1				
DATE DRAWN	BY	CHKD	APVD						
29-Aug-05	JL	MW	MW						
			8-29-05	8-29-05					
NAME								PART No.	
RA POWER JACK, PC								RAPC712X	
Ø0.100 PIN, RoHS								REV	
								A	

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RAPC712X](#) [RAPC712BK](#) [RAPC712TR13X](#) [RAPC712TRP22X](#)