



DATASHEET

FLEXIBLE TOGGLE LATCH 40044 ZI

PICTURES

DESCRIPTION:

Toggle latch with a 4 mm wire link and the facility to padlock secure.

Recommended for seamless assemblies where rigid toggle latches are unsuitable.

Approximate mounting dimension with the catch plate: 63.3 mm for a tension of approx. 50 daN

Maximum operating tension: 70 daN

Suitable for screw fixing using 2 x M4 screws for latch and 2 x M5 screws for catch

Hand operated and easy to use toggle and fastener clamp

Draw latch with over center fastener

Supplied with dimensions template for marking out + catch plate

FEATURES:

- Finish: Zinc Plated
- Material: Steel
- Dimensions: 84 x 25 x 17 mm
- Height: 84 mm
- Width: 25 mm
- Depth: 17 mm

