



DATASHEET

FLEXIBLE TOGGLE LATCH 41002 ZI

PICTURES

DESCRIPTION:

Complete folding of the hook along the lever

Very high tensile strength

Lever lock to prevent accidental opening

High resistance to vibration and shock

Possibility of sealing

Large support surface for the hooking lug

Approximate mounting dimension with catch plate: $x = 90$ mm for a tension of approx. 300 daN

Maximum tension in use: 350 daN

Maximum tension before deformation: 450 daN

Supplied with catch plate

FEATURES:

- Finish: Zinc Plated
- Material: Steel
- Dimensions: 70 x 19 mm
- Width: 70 mm
- Depth: 19mm

