


electrical connection box VAVE-L1-1VR8-LP

Part number: 573919

★ Core product range

FESTO



Data sheet

Feature	Value
Assembly position	Any
Polarity protected	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	12 V 24 V
Surge strength	0.8 kV
Degree of contamination	3
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Protection class	IP65
Ambient temperature	-5 ... 60 °C
Max. tightening torque	0.27 Nm
Product weight	3.2 g
Electrical connection	Plug / socket M8 / - 3-pin/2-pin
Protective earth connection	Not available
Mounting type	On solenoid valve with self-tapping screw
Housing colour	Black
Materials note	Conforms to RoHS
Material housing	PA