

Specification Sheet

Part Number: 156-00068

Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.



Heavy Duty Cable Tie/Fir Tree Mount, 8.75 - 9.25 mm Hole Dia, .04"-.26" Panel Thickness, PA66HIRHSUV, Black,100/pkg

Article Number 156-00068

Type WSSFT9A

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Short Description Heavy Duty Cable Tie/Fir Tree Mount, 8.75 - 9.25 mm Hole Dia, .04"-.26" Panel Thickness, PA66HIRHSUV, Black,100/pkg

Global Part Name

WSSFT9A-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 120.0

Minimum Tensile Strength (Metric) 535

Length L (Imperial) 9.0

Length L (Metric) 228.0

Fixation Method Fir Tree

Identification Plate Position none

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.5

Width W (Metric) 12.7

Bundle Diameter Max (Imperial) 2.3

Bundle Diameter Max (Metric) 57.0

Height H (Imperial) .75

Height H (Metric) 19.10

Panel Thickness Min (Imperial) 0.039

Panel Thickness Max (Imperial)	0.256
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	6.5
Mounting Hole Diameter D (Imperial)	0.34 - 0.36
Mounting Hole Diameter D (Metric)	8.7 - 9.2 mm
Mounting Hole Diameter D Min (Imperial)	0.34
Mounting Hole Diameter D Max (Imperial)	0.36
Mounting Hole Diameter D Max (Metric)	9.25
Disc Diameter (Metric)	21.6
Disc Diameter (Imperial)	0.9
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Material Cable Tie	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Flammability	UL 94 HB

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988